RLCO-940-4000-TO3



TECHNICAL DATA

High Power Infrared Laser Diode

Features

Lasing Mode Structure: multi mode
Peak Wavelength: typ. 940 nm
Optical Ouput Power: 4 W

Package: TO-3, without Photodiode



Electrical Connection

| Pin Configuration | | | Bottom View |
|-------------------|-----|---------------------------------|-------------|
| Ŷ ₁ | | | \bigcirc |
| | PIN | Function | () |
| Δ | 1 | LD Cathode (isolated from case) | (12) |
| | 2 | LD Anode | |
| ² | | | \o\ |

Absolute Maximum Ratings

| Item | Symbol | Value | Unit |
|----------------------------|------------------|---------|------|
| CW Output Power | Po | 5 | W |
| Operating Case Temperature | T _C | -10 +25 | °C |
| Storage Temperature | T _{stq} | -20 +80 | °C |

Specifications

| Item | Symbol | Min. | Тур. | Max. | Unit | | | |
|------------------------------------|-----------------|------|------|------|-------|--|--|--|
| Optical Specifications | | | | | | | | |
| CW Output Power | Po | - | 4 | - | W | | | |
| Center Wavelength | λ_{C} | 937 | 940 | 943 | nm | | | |
| Spectral Width (FWHM) | Δλ | - | 3 | - | nm | | | |
| Wavelength Temperature Coefficient | ∂λ / ∂Τ | - | 0.3 | - | nm/°C | | | |
| EWINA Been Divergence | θ∥ | - | 9 | - | deg | | | |
| FWHM Beam Divergence | θ⊥ | - | 32 | 35 | deg | | | |
| Cavity Length | | - | 2000 | - | μm | | | |
| Emitting Width | W | - | 200 | - | μm | | | |
| Polarization Ratio (TE) | | - | 95 | - | % | | | |
| Electrical Specifications | | | | | | | | |
| Threshold Current | I _{th} | - | 0.7 | - | Α | | | |
| Operating Current | l _{op} | - | 5 | - | Α | | | |
| Power Conversion Efficiency | | 40 | - | - | % | | | |
| Slope Efficiency | η | - | 0.9 | - | W/A | | | |
| Operating Voltage | U_{op} | - | 1.9 | - | V | | | |

The above specifications are for reference purpose only and subjected to change without prior notice.




ROITHNER LASERTECHNIK GIRDH

WIEDNER HAUPTSTRASSE 76 IO40 VIENNA AUSTRIA
TEL. +43 I 586 52 43 -0, FAX. -44, OFFICE@ROITHNER-LASER.COM



Package Dimensons



Safety of Laser light

Laser Light can damage the human eyes and skin. Do not expose the
eye or skin directly to any laser light and/or through optical lens. When
handling the LDs, wear appropriate safety glasses to prevent laser
light, even any reflections from entering to the eye. Focused laser
beam through optical instruments will increase the chance of eye
hazard.



• This LD is emitting invisible light.

Cautions

1. Operating methode

- This LD shall change its forward voltage requirement and optical ouput power according to temperature change. Also, the LD will require more operation current to maintain same ouput power as it degrades.
- Confirm that electrical spike current generated by switching on and off does not exceed the
 maximum operating current level specified herein above as absolute maximum rating. Also,
 employ appropriat countermeasures to reduce chattering and/or overshooting in the circuit.

2. Static Electricity

• Static electricity or electrical surges will reduce and degrade the reliability of the LDs. It is recommended to use a wrist trap or anti-electrostatic glove when handeling the product.

3. Absolute Maximum Rating

Active layer of LDs shall have high current density and generate high electric field during its
operation. In order to prevent excessive damage, the LD must be operated strictly below
absolute maximum rating.

